




Classic filament LEDbulbs

CLA LEDBulb ND 8-75W E27 CW A60 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information		Power Consumption	
Cap-Base	E27 [E27]	8 W	
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	
Switching Cycle	20,000	60 mA	
Lighting Technology	LED	Wattage Equivalent	
EU RoHS compliant	Yes	75 W	
Light Technical		Starting Time (Nom)	
Color Code	840 [CCT of 4000K]	0.5 s	
Luminous Flux	1,055 lm	Warm-up time to 60% light	
Color Designation	Cool White (CW)	0.5 s	
Correlated Color Temperature (Nom)	4000 K	Power Factor (Fraction)	
Luminous Efficacy (rated) (Nom)	131.88 lm/W	0.5	
Color Consistency	<6	Voltage (Nom)	
Color rendering index (CRI)	80	220-240 V	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Temperature	
Operating and Electrical		T-Case Maximum (Nom)	
Line Frequency	50 to 60 Hz	48 °C	
Input Frequency	50 to 60 Hz	Controls and Dimming	
		Dimmable	
		No	
		Mechanical and Housing	
		Bulb Finish	
		Clear	
		Bulb Shape	
		A60 [A 60mm]	
		Approval and Application	
		Energy Consumption kWh/1000 h	
		8 kWh	

Classic filament LEDbulbs

EyeComfort	Yes
Product Data	
Order product name	CLA LEDBulb ND 8-75W E27 CW A60 CL
Full product name	CLA LEDBulb ND 8-75W E27 CW A60 CL
Full product code	871869674261700
Order code	929001384102


Material Nr. (12NC)	929001384102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696742617
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696742624

Dimensional drawing




Product	D	C
CLA LEDBulb ND 8-75W E27 CW A60 CL	60 mm	104 mm

Photometric data



General uniform lighting - CLA LEDBulb ND 8-75W E27 CW A60 CL


Light Distribution Diagram - CLA LEDBulb ND 8-75W E27 CW A60 CL



Spectral Power Distribution Colour - CLA LEDBulb ND 8-75W E27 CW A60 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb ND 8-75W E27 CW A60 CL

Lumen Maintenance Diagram - CLA LEDBulb ND 8-75W E27 CW A60 CL

