



# Classic filament LEDbulbs

## LEDClassic 7-70W A60 E27 WW CL ND APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

<b>General Information</b>			
Cap-Base	E27 [E27]	Power Consumption	7 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	60 mA
Switching Cycle	20,000	Wattage Equivalent	70 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
<b>Light Technical</b>			
Color Code	827 [CCT of 2700K]	<b>Controls and Dimming</b>	
Luminous Flux	806 lm	Dimmable	No
Color Designation	Warm White (WW)		
Correlated Color Temperature (Nom)	2700 K	<b>Mechanical and Housing</b>	
Luminous Efficacy (rated) (Nom)	115.00 lm/W	Bulb Finish	Clear
Color Consistency	<6	Bulb Shape	A60 [A 60mm]
Color rendering index (CRI)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %	<b>Approval and Application</b>	
		Energy Consumption kWh/1000 h	7 kWh
<b>Operating and Electrical</b>		EPREL Registration Number	387390
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs


Product Data	
Order product name	LEDClassic 7-70W A60 E27 WW CL ND APR
Full product name	LEDClassic 7-70W A60 E27 WW CL ND APR
Full product code	871869676526500
Order code	929001387318
Material Nr. (12NC)	929001387318

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696765265
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696765272


Dimensional drawing

Product	D	C
LEDClassic 7-70W A60 E27 WW CL ND APR	60 mm	104 mm


Photometric data



General uniform lighting - LEDClassic 7-70W A60 E27 WW CL ND APR




Spectral Power Distribution Colour - LEDClassic 7-70W A60 E27 WW CL ND APR



Light Distribution Diagram - LEDClassic 7-70W A60 E27 WW CL ND APR

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDClassic 7-70W A60 E27 WW CL ND APR

Lumen Maintenance Diagram - LEDClassic 7-70W A60 E27 WW CL ND APR

