



Classic filament LEDbulbs



CLA LEDBulb ND 7-60W B22 WW ST64 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information		Input Frequency		50 to 60 Hz
Cap-Base	B22 [B22]	Power Consumption		7 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)		60 mA
Switching Cycle	20,000	Wattage Equivalent		60 W
Lighting Technology	LED	Starting Time (Nom)		0.5 s
Flux measurement reference	Sphere	Warm-up time to 60% light		0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)		0.5
Light Technical		Voltage (Nom)		220-240 V
Color Code	827 [CCT of 2700K]	Temperature		
Luminous Flux	806 lm	T-Case Maximum (Nom)		45 °C
Color Designation	Warm White (WW)	Controls and Dimming		
Correlated Color Temperature (Nom)	2700 K	Dimmable		No
Luminous Efficacy (rated) (Nom)	115.00 lm/W	Mechanical and Housing		
Color Consistency	<6	Bulb Finish		Clear
Color rendering index (CRI)	80	Bulb Shape		ST64
LLMF At End Of Nominal Lifetime (Nom)	70 %			
Operating and Electrical				
Line Frequency	50 to 60 Hz			

Classic filament LEDbulbs

Approval and Application	
Energy Efficiency Class	E
Energy Consumption kWh/1000 h	7 kWh
EPREL Registration Number	387393
EyeComfort	Yes
Product Data	
Order product name	CLA LEDBulb ND 7-60W B22 WW ST64 CL
Full product name	CLA LEDBulb ND 7-60W B22 WW ST64 CL


Full product code	871869674279200
Order code	929001387702
Material Nr. (12NC)	929001387702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696742792
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696742808

Dimensional drawing



Product	D	C
CLA LEDBulb ND 7-60W B22 WW ST64 CL	64 mm	138 mm

Photometric data




General uniform lighting - CLA LEDBulb ND 7-60W B22 WW ST64 CL

Spectral Power Distribution Colour - CLA LEDBulb ND 7-60W B22 WW ST64 CL


Classic filament LEDbulbs

Photometric data



Light Distribution Diagram - CLA LEDBulb ND 7-60W B22 WW ST64 CL

Lifetime



Life Expectancy Diagram - CLA LEDBulb ND 7-60W B22 WW ST64 CL

Lumen Maintenance Diagram - CLA LEDBulb ND 7-60W B22 WW ST64 CL

