



Classic filament LEDbulbs

LEDClassic 7-70W G93 E27 WW CL ND APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	115.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz


Power Consumption	7 W
Lamp Current (Nom)	60 mA
Wattage Equivalent	70 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	G93 [G 93mm]
Approval and Application	
Energy Consumption kWh/1000 h	7 kWh
Product Data	
Order product name	LEDClassic 7-70W G93 E27 WW CL ND APR

Classic filament LEDbulbs

Full product name	LEDClassic 7-70W G93 E27 WW CL ND APR
Full product code	871869676532600
Order code	929001387918
Material Nr. (12NC)	929001387918
Numerator - Quantity Per Pack	1



EAN/UPC - Product/Case	8718696765326
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696765333

Dimensional drawing




Product	D	C
LEDClassic 7-70W G93 E27 WW CL ND APR	95 mm	140 mm

Photometric data



General uniform lighting - LEDClassic 7-70W G93 E27 WW CL ND APR


Spectral Power Distribution Colour - LEDClassic 7-70W G93 E27 WW CL ND APR




Light Distribution Diagram - LEDClassic 7-70W G93 E27 WW CL ND APR

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDClassic 7-70W G93 E27 WW CL ND APR



Lumen Maintenance Diagram - LEDClassic 7-70W G93 E27 WW CL ND APR

