



CorePro LED PL 4pin 2pin

8.5PL-C/T LED/26H-3000 IF 4P 10/1

The CorePro LED Type A - Ballast Driven (Plug and Play) InstantFit CFL-ni is a great LED solution suitable for replacing both 2-pin and 4-pin CFL fluorescent lamps, using an existing ballast. Both vertical and horizontal options are available with the horizontal version having a rotatable end cap to ensure the light is correctly aimed.

Product data

General Information	
Cap-Base	G24Q/GX24Q [G24q/GX24q]
Main Application	Industrial
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
B50L70	50000 h
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	900 lm
Luminous Flux (Rated) (Nom)	900 lm
Correlated Color Temperature (Nom)	3000 K
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	20000-100000 Hz
Power (Rated) (Nom)	8.5 W
Lamp Current (Max)	550 mA

Lamp Current (Min)	150 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	60 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	200 mm

CorePro LED PL 4pin 2pin

Approval and Application


Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance KEMA Keur certificate DLC compliance
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List

Product Data

Order product name	8.5PL-C/T LED/26H-3000 IF 4P 10/1
--------------------	-----------------------------------

EAN/UPC - Product	046677458379
Order code	929001388104
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001388104
Net Weight (Piece)	0.082 kg


Dimensional drawing



PLED PLC 120V 8.5-26W 1000lm 3000K GX24q


Product	D1	D2	A1	A2	A3
8.5PL-C/T LED/26H-3000 IF 4P 10/1	24.3 mm	28.4 mm	128.3 mm	147.5 mm	163.1 mm

Photometric data



General Uniform Lighting
1 x PL-C 4 PIN JENSEN LED 26W/3000K
Page 10


LEDtube PLC 100mm 9W G24Q GX24Q 830 900lm



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm


CorePro LED PL 4pin 2pin

Photometric data




LEDtube VLE 600 mm 10 W /830 T8 ROT


Lifetime




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

CorePro LED PL 4pin 2pin

Lifetime



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

