



PL-C/T

10.5PL-C/T LED/26V-3000 IF 4P 1PK 10/1

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Product data

General Information		Power Factor (Nom)	
Base	G24Q/GX24Q [G24q/GX24q]		0.9
EU RoHS compliant	Yes	Voltage (Nom)	120 V
Nominal Lifetime (Nom)	50000 h	Temperature	
Switching Cycle	50000X	T-Ambient (Max)	45 °C
Light Technical		T-Ambient (Min)	-20 °C
Color Code	830 [CCT of 3000K]	T-Storage (Max)	65 °C
Initial lumen (Nom)	1200 lm	T-Storage (Min)	-40 °C
Correlated Color Temperature (Nom)	3000 K	T-Case Maximum (Nom)	60 °C
Luminous Efficacy (rated) (Nom)	114.00 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	Yes
Color Rendering Index (Nom)	82	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Length	100 mm
Operating and Electrical		Approval and Application	
Input Frequency	20000-100000 Hz	Energy Saving Product	Yes
Power (Rated) (Nom)	10.5 W	Approbation Marks	RoHS compliance UL certificate KEMA Keur certificate DLC compliance
Lamp Current (Max)	550 mA	Energy Certifications	DLC Standard
Lamp Current (Min)	150 mA		
Starting Time (Nom)	0.5 s		
Warm Up Time to 60% Light (Nom)	0.5 s		

PL-C/T


DesignLights Consortium Qualified Product List -

Product Data

XUCDM.COPY.Product.Title	10.5PL-C/T LED/26V-3000 IF 4P 10/1
EAN/UPC - Product	046677458416
Order code	458414
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001388504
Net Weight (Piece)	0.091 kg
Model Number	9290013885



Dimensional drawing



PLED PLC 10.5-26W 1300lm 3000K GX24q


Product	D1	D2	A1	A2	A3
10.5PL-C/T LED/26V-3000 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm

Photometric data





LEDtube PLC 100mm 11W G24Q GX24Q 830 1200lm

LEDtube PLC 100mm 11W G24Q GX24Q 827 1200lm





Lifetime




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 11W G24Q GX24Q 827 1200lm

