



PL-C/T

10.5PL-C/T LED/26V-3500 IF 4P 1PK 10/1

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Product data


General Information		Starting Time (Nom)	
Cap-Base	G24Q/GX24Q [G24q/GX24q]		0.5 s
Main Application	Industrial	Warm Up Time to 60% Light (Nom)	0.5 s
Nominal Lifetime (Nom)	50000 h	Power Factor (Nom)	0.9
Switching Cycle	50000X	Voltage (Nom)	120 V
B50L70	50000 h		
Light Technical		Temperature	
Color Code	835 [CCT of 3500K]	T-Ambient (Max)	45 °C
Luminous Flux (Nom)	1200 lm	T-Ambient (Min)	-20 °C
Luminous Flux (Rated) (Nom)	1200 lm	T-Storage (Max)	65 °C
Correlated Color Temperature (Nom)	3500 K	T-Storage (Min)	-40 °C
Luminous Efficacy (rated) (Nom)	114.00 lm/W	T-Case Maximum (Nom)	60 °C
Color Consistency	<6		
Color Rendering Index (Nom)	82	Controls and Dimming	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Dimmable	Yes
Operating and Electrical		Mechanical and Housing	
Input Frequency	20000-100000 Hz	Product Length	100 mm
Power (Rated) (Nom)	10.5 W		
Lamp Current (Max)	550 mA	Approval and Application	
Lamp Current (Min)	150 mA	Energy Saving Product	Yes
		Approval Marks	RoHS compliance UL certificate KEMA Keur certificate DLC compliance

PL-C/T

Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-
Product Data	
Order product name	10.5PL-C/T LED/26V-3500 IF 4P 10/1
EAN/UPC - Product	046677458423

Order code	458422
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001388604
Net Weight (Piece)	0.091 kg


Dimensional drawing




PLED PLC 10.5-26W 1200lm 3500K GX24q

Product	D1	D2	A1	A2	A3
10.5PL-C/T LED/26V-3500 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm


Photometric data



LEDtube PLC 100mm 11W G24Q GX24Q 835 1200lm





LEDtube PLC 100mm 11W G24Q GX24Q 835 1200lm





LEDtube PLC 100mm 11W G24Q GX24Q 827 1200lm

Lifetime




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 11W G24Q GX24Q 827 1200lm

