

PL-C/T

10.5PL-C/T LED/26V-4000 IF 4P 1PK 10/1

Philips PLED 4-pin & 2-pin lamps are an affordable LED solution to replace compact fluorescent lamps. The product provides a natural lighting effect for use in many lighting applications, and provides instant energy savings, making them an environmentally-friendly solution. Available as replacements for 13W, 26W and 32W compact fluorescent lamps.

Product data


General Information		Starting Time (Nom)	
Base	G24Q/GX24Q [G24q/GX24q]	Starting Time (Nom)	0.5 s
Main Application	Industrial	Warm Up Time to 60% Light (Nom)	0.5 s
Nominal Lifetime (Nom)	50000 h	Power Factor (Nom)	0.9
Switching Cycle	50000X	Voltage (Nom)	120 V
B50L70	50000 h	Temperature	
Light Technical		T-Ambient (Max)	45 °C
Color Code	841 [CCT of 4100K (841)]	T-Ambient (Min)	-20 °C
Initial lumen (Nom)	1300 lm	T-Storage (Max)	65 °C
Luminous Flux (Rated) (Nom)	1300 lm	T-Storage (Min)	-40 °C
Correlated Color Temperature (Nom)	4000 K	T-Case Maximum (Nom)	60 °C
Luminous Efficacy (rated) (Nom)	123.00 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	Yes
Color Rendering Index (Nom)	82	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Product Length	100 mm
Operating and Electrical		Approval and Application	
Input Frequency	20000-100000 Hz	Energy Saving Product	Yes
Power (Rated) (Nom)	10.5 W	Approbation Marks	RoHS compliance UL certificate KEMA Keur certificate DLC compliance
Lamp Current (Max)	550 mA		
Lamp Current (Min)	150 mA		

PL-C/T

Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-
Product Data	
Order product name	10.5PL-C/T LED/26V-4000 IF 4P 10/1
EAN/UPC - Product	046677458430
Order code	458430

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001388704
Net Weight (Piece)	0.091 kg
Model Number	9290013887



Dimensional drawing



PLED PLC 10.5-26W 1200lm 4000K GX24q

Product	D1	D2	A1	A2	A3
10.5PL-C/T LED/26V-4000 IF 4P 10/1	24.3 mm	29 mm	99.9 mm	109.9 mm	125.5 mm


Photometric data



General Lighting
10.5PL-C/T LED/26V-4000 IF 4P 10/1



LEDtube PLC 100mm 11W G24Q GX24Q 840 1300lm

LEDtube PLC 100mm 11W G24Q GX24Q 840 1300lm





LEDtube PLC 100mm 11W G24Q GX24Q 827 1200lm

Lifetime




LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm

LEDtube PLC 100mm 9W G24Q GX24Q 827 850lm



LEDtube PLC 100mm 11W G24Q GX24Q 827 1200lm

