



# MASTER LEDtube InstantFit HF T5

## MAS LEDtube HF 1500mm HE 20W 840 T5

Philips MASTER LEDtube InstantFit T5 integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescents. The Philips MASTER LEDtube InstantFit T5 is the ideal solution for customers who have higher light output requirements and want to maximise value over the lifetime. The full energy savings & longer lifetime result in attractive payback times and TCO benefits.

### Product data

General Information	
Cap base	G5 [ G5]
Nominal lifetime (nom.)	50000 h
Switching cycle	50000X
B50L70	50000 h

Light Technical	
Colour code	840 [ CCT of 4,000 K]
Luminous flux (nom.)	3000 lm
Luminous flux (rated) (nom.)	3000 lm
Correlated colour temperature (nom.)	4000 K
Colour consistency	<6
Color rendering index (nom.)	83
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	35000-70000 Hz
Power (Rated) (Nom)	20 W
Lamp current (max.)	350 mA

Lamp current (min.)	150 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	120-160 V

Temperature	
T ambient (max.)	45 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	65 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Product length	1500 mm

# MASTER LEDtube InstantFit HF T5

## Approval and Application


Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	24 kWh

## Product Data

Full product code	871869674337900
-------------------	-----------------

Order product name	MAS LEDtube HF 1500mm HE 20W 840 T5
EAN/UPC – product	8718696743379
Order code	74337900
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001391402
Net weight (piece)	0.196 kg


## Dimensional drawing



TLED 1500mm 230V17W-35W 2600lm 160D 400


Product	D1	D2	A1	A2	A3
MAS LEDtube HF 1500mm HE 20W 840 T5	15.5 mm	18.8 mm	1449 mm	1456.1 mm	1463.2 mm

## Photometric data



General Information 14 Recycling 14 Page 14

LEDtube 1500mm 20W G5 840 3000lm



LEDtube 1500mm 20W G5 840 3000lm

# MASTER LEDtube InstantFit HF T5

## Photometric data




LEDtube 600mm 8W G5 830 1000lm

## Lifetime




LEDtube 600mm 8W G5 830 1000lm



LEDtube 600mm 8W G5 830 1000lm



LEDtube 600mm 8W G5 830 1000lm



LEDtube 600mm 8W G5 830 1000lm

# MASTER LEDtube InstantFit HF T5

## Lifetime



LEDtube 600mm 8W G5 830 1000lm

