



# LED Urban TrueForce Lamps

## 55ED28/LED/730/ND 120-277V G2 4/1

Philips TrueForce LED high lumen post top lamp makes it easy to upgrade to long lasting, energy saving LED technology without sacrificing your site's unique outdoor character. Philips TrueForce is a direct replacement option which ensures a perfect fit with existing modern and traditional luminaires. We claim true replacement when comparing flux. This post top lamps can be used in enclosed fixtures.

### Product data

General Information	
Base	E39 [ Single Contact Mogul Screw]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	55-150W
Light Technical	
Color Code	730 [ CCT of 3000K]
Beam Angle (Nom)	360 °
Initial lumen (Nom)	8000 lm
Luminous Flux (Rated) (Nom)	8000 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	133.33 lm/W
Color Consistency	ANSI 3000K
Color Rendering Index (Nom)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	55 W
Lamp Current (Nom)	460 mA
Wattage Equivalent	150 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear (CL)

# LED Urban TrueForce Lamps

## Approval and Application


Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-

## Product Data

Order product name	55ED28/LED/730/ND 120-277V G2 4/1
EAN/UPC - Product	046677473631

Order code	473637
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001396804
Net Weight (Piece)	0.900 kg


## Dimensional drawing




HIB NAM Post top 8000lm 3000K G2

Product	D	C
55ED28/LED/730/ND 120-277V G2 4/1	105 mm	204 mm


## Photometric data



High Intensity 40W E39 ED-28 Clear 3000K




HIB NAM Trueforce 55W E39 Clear 730 36D ND




HIB NAM Trueforce 55W E39 Clear 730 36D ND

# LED Urban TrueForce Lamps

## Lifetime



HIB NAM Trueforce 26W E26 Clear 730 36D ND



HIB NAM Trueforce 26W E26 Clear 730 36D ND

