

T8

10T8 LED/48-5000 IF 1PK 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

| General information | |
|---------------------------------------|----------------------------------|
| Base | G13 [Medium Bi-Pin Fluorescent] |
| EU RoHS compliant | Yes |
| Nominal Lifetime (Nom) | 70000 h |
| Switching Cycle | 50000X |
| Light technical | |
| Color Code | 850 [CCT of 5000K] |
| Beam Angle (Nom) | 180 ° |
| Initial lumen (Nom) | 1600 lm |
| Color Designation | Daylight |
| Correlated Color Temperature (Nom) | 5000 K |
| Luminous Efficacy (rated) (Nom) | 160.00 lm/W |
| Color Consistency | <6 |
| Color Rendering Index (Nom) | 82 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Operating and electrical | |
| Input Frequency | 20000-120000 Hz |
| Power (Rated) (Nom) | 10 W |

| | |
|---------------------------------|-----------------|
| Lamp Current (Max) | 340 mA |
| Lamp Current (Min) | 110 mA |
| Starting Time (Nom) | 0.5 s |
| Warm Up Time to 60% Light (Nom) | 0.5 s |
| Power Factor (Nom) | 0.9 |
| Voltage (Nom) | 120-277V; 347 V |

| Temperature | |
|----------------------|--------|
| T-Ambient (Max) | 45 °C |
| T-Ambient (Min) | -20 °C |
| T-Storage (Max) | 65 °C |
| T-Storage (Min) | -40 °C |
| T-Case Maximum (Nom) | 50 °C |

| Controls and dimming | |
|----------------------|----|
| Dimmable | No |


| Mechanical and housing | |
|------------------------|-------|
| Product Length | 48 in |

T8

| | |
|---------------------------------|---|
| Bulb Shape | Tube, double-ended |
| Approval and application | |
| Energy Saving Product | Yes |
| Approbation Marks | UL certificate RoHS compliance DLC compliance |
| Energy Consumption kWh/1000 h | - kWh |
| Energy Certifications | DLC Standard |
| Product data | |
| Order product name | 10T8 LED/48-5000 IF 1PK 10/1 |

| | |
|---------------------------------|--------------|
| EAN/UPC - Product | 046677474003 |
| Order code | 474007 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 10 |
| Material Nr. (12NC) | 929001397504 |
| Net Weight (Piece) | 0.230 kg |
| Model Number | 9290013975 |


Dimensional drawing




10T8 LED/48-5000 IF 1PK 10/1

| Product | D1 | D2 | A1 | A2 | A3 |
|------------------------------|---------|---------|-----------|-----------|-----------|
| 10T8 LED/48-5000 IF 1PK 10/1 | 25.7 mm | 26.3 mm | 1198.1 mm | 1205.2 mm | 1212.3 mm |

Photometric data




LEDtube 1200mm 12W G13 850 1650lm




LEDtube 10W G13 850 IF 1PK

Photometric data




LEDtube 10W G13 827 IF 1PK


Lifetime




LEDtube 10W G13 827-850 IF 1PK



LEDtube 10W G13 827-850 IF 1PK




LEDtube 10W G13 827-850 IF 1PK



LEDtube 10W G13 827-850 IF 1PK

T8

Lifetime



LEDtube 10W G13 827-850 IF 1PK

