

# T8

## 13T8 LED/48-3000 IF DIM 1PK 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	70000 h
Switching Cycle	50000X
Light Technical	
Color Code	830 [ CCT of 3000K]
Beam Angle (Nom)	180 °
Initial lumen (Nom)	2000 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	153.85 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	20000-120000 Hz
Power (Rated) (Nom)	13 W

Lamp Current (Max)	400 mA
Lamp Current (Min)	130 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277V; 347 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Product Length	48 in

# T8

## Approval and Application


Energy Efficiency Label (EEL)	Not applicable
Energy Saving Product	Yes
Approbation Marks	UL certificate RoHS compliance DLC compliance
Energy Consumption kWh/1000 h	- kWh

## Product Data

Order product name	13T8 LED/48-3000 IF DIM 1PK 10/1
--------------------	----------------------------------

EAN/UPC - Product	046677473921
Order code	473926
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001397604
Net Weight (Piece)	0.230 kg
Model Number	9290013976


## Dimensional drawing




TLED IF MasterClass 4ft 2000lm 3000K

Product	D1	D2	A1	A2	A3
13T8 LED/48-3000 IF DIM 1PK 10/1	25.7 mm	26.3 mm	1198.1 mm	1205.2 mm	1212.3 mm

## Photometric data




LEDtube 600mm 8W G5 830 1000lm




LEDtube 13W G13 830 IF DIM

Photometric data




LEDtube 13W G13 2100lm


Lifetime




LEDtube 13W G13 2100lm



LEDtube 13W G13 2100lm




LEDtube 13W G13 2100lm



LEDtube 13W G13 2100lm

# T8

## Lifetime



LEDtube 13W G13 2100lm

