



T8

15T8 LED/24-4000 IF 6U EasySmart 1PK

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information		Input Frequency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	40000-80000 Hz
Nominal lifetime	50,000 hour(s)	Lamp Current (Max)	15 W
Switching Cycle	50,000	Lamp Current (Min)	350 mA
Lighting Technology	LED	Starting Time (Nom)	120 mA
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.9
		Voltage (Nom)	160-380 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	Ambient temperature range	-20 °C to 45 °C
Beam Angle (Nom)	160 degree(s)	T-Case Maximum (Nom)	40 °C
Luminous Flux	2,100 lm		
Color Designation	Cool White (CW)	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	Wireless Dim
Luminous Efficacy (rated) (Nom)	140.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Product Length	600 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	Tube, double-ended
Operating and Electrical			
Line Frequency	40000-80000 Hz		

Approval and Application


Energy Saving Product	Yes
Approval Marks	UL certificate RoHS compliance DLC compliance
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	DLC Standard

Product Data

Order product name	15T8 LED/24-4000 IF 6U EasySmart 1PK
--------------------	--------------------------------------



Full product name	15T8 LED/24-4000 IF 6U EasySmart 1PK
Order code	929001398204
Material Nr. (12NC)	929001398204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677474034
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677474039

Dimensional drawing




Product	D1	D2	B	A1	D
15T8 LED/24-4000 IF 6U EasySmart 1PK	25.4 mm	27.8 mm	152 mm	570 mm	27.8 mm

Photometric data



Spectral Power Distribution Colour - 15T8 LED/24-4000 IF 6U EasySmart 1PK


Light Distribution Diagram - 15T8 LED/24-4000 IF 6U EasySmart 1PK




General uniform lighting - 15T8 LED/24-4000 IF 6U EasySmart 1PK

T8

Lifetime




Life Expectancy Diagram - 15T8 LED/24-4000 IF 6U EasySmart 1PK



Life Expectancy Diagram - 15T8 LED/24-4000 IF 6U EasySmart 1PK

Life Expectancy Diagram - 15T8 LED/24-4000 IF 6U EasySmart 1PK



Lumen Maintenance Diagram - 15T8 LED/24-4000 IF 6U EasySmart 1PK

Lumen Maintenance Diagram - 15T8 LED/24-4000 IF 6U EasySmart 1PK

