



# Interact

## 15T8/24-840/IF21-6U/MAScon IA 10/1

### Product data

General Information	
Base	G13 [ Medium Bi-Pin Fluorescent]
Main Application	Office
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
B50L70	50000 h
Light Technical	
Color Code	841 [ CCT of 4100K (841)]
Beam Angle (Nom)	160 °
Initial lumen (Nom)	2100 lm
Luminous Flux (Rated) (Nom)	2100 lm
Rated Beam Angle	160 °
Correlated Color Temperature (Nom)	4000 K
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	40000-80000 Hz
Power (Rated) (Nom)	15 W
Lamp Current (Max)	350 mA
Lamp Current (Min)	120 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9

Voltage (Nom)	160-380 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	40 °C

Controls and Dimming	
Dimmable	Wireless Dim

Mechanical and Housing	
Product Length	600 mm

Approval and Application	
Energy Saving Product	Yes
Approbation Marks	UL certificate RoHS compliance DLC compliance
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-


Product Data	
Order product name	15T8/24-840/IF21-6U/MAScon IA 10/1
EAN/UPC - Product	046677537234
Order code	537233
Numerator - Quantity Per Pack	1

# Interact

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001398264
Net Weight (Piece)	0.270 kg

Model Number	9290013982
--------------	------------



## Dimensional drawing



Product	D1	D2	B	A1	D
15T8/24-840/IF21-6U/MAScon	25.4 mm	27.8 mm	152 mm	570 mm	27.8 mm
IA 10/1					


TLED SMART 4ft HF 14-32W 2100lm 4000K

## Photometric data



LEDtube 600mm 8W G5 840 1050lm



LEDtube 15W G13 830 160D IF 6U EasySmart



LEDtube 15W G13 840 160D IF 6U EasySmart



# Interact

## Lifetime




LEDtube 15W G13 830-850 160D IF 6U EasySmart

LEDtube 15W G13 830-850 160D IF 6U EasySmart



LEDtube 15W G13 830-850 160D IF 6U EasySmart

LEDtube 15W G13 830-850 160D IF 6U EasySmart



LEDtube 15W G13 830-850 160D IF 6U EasySmart

