



# Classic filament LED candles and lustres

## CLA LEDCandle ND 4-40W B35 B15 827 CL

Featuring a classic heritage design, filament LED candles and lustres combine the familiar shapes of classic incandescent candles or lustres with the benefits of long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lustres.

### Product data

General Information	
Cap base	B15 [ B15]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	4-40W
Light Technical	
Colour code	827 [ CCT of 2,700 K]
Luminous flux (nom.)	470 lm
Luminous flux (rated) (nom.)	470 lm
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	118.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	4 W

Lamp current (nom.)	36 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Clear (CL)
Approval and Application	
Energy efficiency label (EEL)	A++
Energy Consumption kWh/1000 h	4 kWh

# Classic filament LED candles and lustres

## Product Data

Full product code	871869676692700
Order product name	CLA LEDCandle ND 4-40W B35 B15 827 CL
EAN/UPC – product	8718696766927
Order code	76692700
Numerator – quantity per pack	1



Numerator – packs per outer box	10
Material no. (12NC)	929001815702
Net weight (piece)	0.010 kg

## Dimensional drawing


Product	D	C
CLA LEDCandle ND 4-40W B35 B15 827 CL	35 mm	97 mm

## Candle 230V 4-40W 470lm 2700K B15 ND B35

## Photometric data




## CLA LEDcandle 40W B15 827 CL B35




## Classic filament LED candles and lustres

### Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

