



Classic filament LED candles and lusters

CLA LEDCandle ND 4-40W B35 B22 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data


General Information		Power Consumption	
Cap-Base	B22 [B22]	4 W	
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	
Switching Cycle	20,000	36 mA	
Lighting Technology	LED	Wattage Equivalent	
EU RoHS compliant	Yes	40 W	
Light Technical		Starting Time (Nom)	
Color Code	827 [CCT of 2700K]	0.5 s	
Luminous Flux	470 lm	Warm-up time to 60% light	
Color Designation	Warm White (WW)	0.5 s	
Correlated Color Temperature (Nom)	2700 K	Power Factor (Fraction)	
Luminous Efficacy (rated) (Nom)	118.00 lm/W	0.4	
Color Consistency	<6	Voltage (Nom)	
Color rendering index (CRI)	80	220-240 V	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Temperature	
Operating and Electrical		T-Case Maximum (Nom)	
Line Frequency	50 to 60 Hz	45 °C	
Input Frequency	50 to 60 Hz	Controls and Dimming	
		Dimmable	
		No	
		Mechanical and Housing	
		Bulb Finish	
		Clear	
		Bulb Shape	
		B35 [B 35mm]	

Classic filament LED candles and lusters

Approval and Application	
Energy Consumption kWh/1000 h	4 kWh
Product Data	
Order product name	CLA LEDCandle ND 4-40W B35 B22 827 CL
Full product name	CLA LEDCandle ND 4-40W B35 B22 827 CL
Full product code	871869676694100
Order code	929001815802


Material Nr. (12NC)	929001815802
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696766941
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696766958

Dimensional drawing




Product	D	C
CLA LEDCandle ND 4-40W B35 B22 827 CL	35 mm	93 mm

Photometric data



General uniform lighting - CLA LEDCandle ND 4-40W B35 B22 827 CL




Spectral Power Distribution Colour - CLA LEDCandle ND 4-40W B35 B22 827 CL

Light Distribution Diagram - CLA LEDCandle ND 4-40W B35 B22 827 CL

Classic filament LED candles and lusters

Lifetime



Life Expectancy Diagram - CLA LEDCandle ND 4-40W B35 B22 827 CL

Lumen Maintenance Diagram - CLA LEDCandle ND 4-40W B35 B22 827 CL

