



CorePro LEDcapsule LV

CorePro LEDcapsuleLV 1.7-20W G4 830

The CorePro LEDcapsule is a true alternative to the halogen capsule. It is particularly suitable for task lighting and decorative applications in homes, shops, hotels and restaurants. Compatible with existing fixtures with G4 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers significant energy savings and minimises maintenance costs without any compromise on light quality.

Product data


General Information		Operating and Electrical	
Cap base	G4 [G4]	Power (Rated) (Nom)	1.7 W
RoHS mark	RoHS mark	Lamp current (nom.)	240 mA
Nominal lifetime (nom.)	15000 h	Wattage equivalent	20 W
Switching cycle	50000X	Starting time (nom.)	0.5 s
Technical type	1.7-20W	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.5
		Voltage (Nom)	12 V
Light Technical		Temperature	
Colour Code	830 [CCT of 3,000 K]	T-Case maximum (nom.)	56 °C
Lamp Luminous Flux 25°C EL (Nom)	205 lm		
Lamp Luminous Flux (Nom)	205 lm	Controls and Dimming	
Colour Designation	White (WH)	Dimmable	No
Colour Temperature, horizontal (Nom)	3000 K	Approval and Application	
Lamp Luminous Efficacy EM (Nom)	120.00 lm/W	Energy efficiency label (EEL)	A++
Colour consistency	<6	Suitable for accent lighting	No
Colour Rendering Index,horiz (Nom)	80		
LLMF at end of nominal lifetime (nom.)	70 %		

CorePro LEDcapsule LV

Energy Consumption kWh/1000 h	2 kWh
Product Data	
Full product code	871869679308400
Order product name	CorePro LEDcapsuleLV 1.7-20W G4 830
EAN/UPC – product	8718696793084
Order code	929001844202

Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	929001844202
Net weight (piece)	0.008 kg



Dimensional drawing



Capsule 12V2W-20W 200lm N.AD 3000K G4


Product	D	C
CorePro LEDcapsuleLV 1.7-20W G4 830	14.5 mm	38 mm

Photometric data



LEDcapsule CorePro 0.9-10W G4 Capsule 827 ND



LEDcapsule CorePro 1.7-20W G4 Capsule 830 ND



LEDcapsule CorePro 0.9-10W G4 Capsule 830 ND

CorePro LEDcapsule LV

Lifetime



LEDcapsule CorePro 0.9-10W G4 Capsule 830 ND

LEDcapsule CorePro 0.9-10W G4 Capsule 830 ND

