

T8

14T8/COR/48-830/MF17/G 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.


Product data

General Information		Input Frequency	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Power Consumption	14 W
Nominal lifetime	50,000 hour(s)	Lamp Current (Max)	130 mA
Switching Cycle	50,000	Lamp Current (Min)	47 mA
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.9
Color Code	830 [CCT of 3000K]	Voltage (Nom)	120-277 V
Beam Angle (Nom)	240 degree(s)	UL Type	Type B - bypass the ballast
Luminous Flux	1,700 lm	Temperature	
Color Designation	White (WH)	Ambient temperature range	-20 °C to 45 °C
Correlated Color Temperature (Nom)	3000 K	T-Case Maximum (Nom)	70 °C
Luminous Efficacy (rated) (Nom)	121.00 lm/W	Controls and Dimming	
Color Consistency	<6	Dimmable	No
Color rendering index (CRI)	80	Mechanical and Housing	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Glass
Operating and Electrical		Product Length	1,200 mm
Line Frequency	50 to 60 Hz		

Bulb Shape	Tube, double-ended
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	14T8/COR/48-830/MF17/G 10/1


Full product name	14T8/COR/48-830/MF17/G 10/1
Order code	929001845434
Material Nr. (12NC)	929001845434
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677477318
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677477313

Dimensional drawing




Product	D1	D2	A1	A2	A3
14T8/COR/48-830/MF17/G 10/1	25.7 mm	28 mm	1,198 mm	1,205 mm	1,212 mm

Photometric data




Spectral Power Distribution Colour - 14T8/COR/48-830/MF17/G 10/1




General uniform lighting - 14T8/COR/48-830/MF17/G 10/1

Photometric data




Light Distribution Diagram - 14T8/COR/48-830/MF17/G 10/1


Lifetime




Life Expectancy Diagram - 14T8/COR/48-830/MF17/G 10/1



Life Expectancy Diagram - 14T8/COR/48-830/MF17/G 10/1




Life Expectancy Diagram - 14T8/COR/48-830/MF17/G 10/1



Lumen Maintenance Diagram - 14T8/COR/48-830/MF17/G 10/1

Lifetime



Lumen Maintenance Diagram - 14T8/COR/48-830/MF17/G 10/1

