



CorePro LEDtube MainsFit T8

14T8PRO/48-835/BB17/G 10/1 FB

Philips CorePro MainsFit (UL Type-B) T8 LED lamps use a double-ended design which significantly simplifies installation. This ballast bypass product replaces either T8 or T12 lamps in fixtures containing shunted or non-shunted G13 (medium bi-pin) lamp holders for over 40% energy savings.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
B50L70	50000 h

Light Technical	
Color Code	835 [CCT of 3500K]
Beam Angle (Nom)	240 °
Initial lumen (Nom)	1700 lm
Luminous Flux (Rated) (Nom)	1700 lm
Rated Beam Angle	240 °
Correlated Color Temperature (Nom)	3500 K
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz

Power (Rated) (Nom)	14 W
Lamp Current (Max)	130 mA
Lamp Current (Min)	47 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V

Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	70 °C

Controls and Dimming	
Dimmable	No


CorePro LEDtube MainsFit T8

Mechanical and Housing	
Product Length	1200 mm
Approval and Application	
Energy Saving Product	Yes
Approbation Marks	UL certificate RoHS compliance DLC compliance
DesignLights Consortium Qualified Product List	DesignLights Consortium Qualified Product List

Product Data	
Order product name	14T8PRO/48-835/BB17/G 10/1 FB

EAN/UPC - Product	046677477325
Order code	477323
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001845504
Net Weight (Piece)	0.210 kg
Model Number	9290018455


Dimensional drawing




TLED IF CorePro 4ft 1700lm 3500K

Product	D1	D2	A1	A2	A3
14T8PRO/48-835/BB17/G 10/1 FB	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm

Photometric data




LEDtube 8-15W G13 835 160D IF 6U EasySmart



LEDtube 14W G13 835 ND BB17


CorePro LEDtube MainsFit T8

Photometric data




LEDtube 14W G13 830 ND BB17


Lifetime




LEDtube 14W G13 830-850 ND BB17-18



LEDtube 14W G13 830-850 ND BB17-18




LEDtube 14W G13 830-850 ND BB17-18



LEDtube 14W G13 830-850 ND BB17-18

CorePro LEDtube MainsFit T8

Lifetime



LEDtube 14W G13 830-850 ND BB17-18

