



T8

14T8/COR/48-835/MF17/G 10/1

Our TLEDs are available in InstantFit (Type A / Type C) or MainsFit (Ballast bypass / Type B) versions. The InstantFit lamps work on a broad variety of ballasts and LED drivers. Only InstantFit has over 15,000 lamp & ballast combinations delivering even light output, energy savings and a long lifetime. Our MainsFit products feature a double-ended design, simplifying installation while a proprietary safety circuit minimizes a shock risk. Lamp sizes range from 2-foot to 8-foot and U-bend with a variety of lumen outputs.

Product data

General Information	
Base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Light Technical	
Color Code	835 [CCT of 3500K]
Beam Angle (Nom)	240 °
Initial lumen (Nom)	1700 lm
Correlated Color Temperature (Nom)	3500 K
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	14 W
Lamp Current (Max)	130 mA
Lamp Current (Min)	47 mA

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Ambient (Max)	45 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	65 °C
T-Storage (Min)	-40 °C
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	1200 mm
Approval and Application	
Energy Saving Product	Yes

T8

Approbation Marks	RoHS compliance UL certificate DLC compliance
Product Data	
Order product name	14T8/COR/48-835/MF17/G 10/1
EAN/UPC - Product	046677477325
Order code	477323

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001845534
Net Weight (Piece)	0.220 kg
Model Number	9290018455A



Dimensional drawing

A3

Product	D1	D2	A1	A2	A3
14T8/COR/48-835/MF17/G 10/1	25.7 mm	28 mm	1198 mm	1205 mm	1212 mm


TLED IF CorePro 4ft 1700lm 3500K

Photometric data





LEDtube 8-15W G13 835 160D IF 6U EasySmart

LEDtube 14W G13 835 ND BB17





LEDtube 14W G13 830 ND BB17

Lifetime




LEDtube 14W G13 830-850 ND BB17-18

LEDtube 14W G13 830-850 ND BB17-18



LEDtube 14W G13 830-850 ND BB17-18

LEDtube 14W G13 830-850 ND BB17-18



LEDtube 14W G13 830-850 ND BB17-18

