



LED Highbay

150HB/LED/740/ND WB DL BB 2/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.


Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	150-400W
Light Technical	
Color Code	740 [CCT of 4000K]
Beam Angle (Nom)	130 °
Luminous Flux (Nom)	20000 lm
Luminous Flux (Rated) (Nom)	20000 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	133.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	150 W
Lamp Current (Nom)	1250 mA

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-
Product Data	
Order product name	150HB/LED/740/ND WB DL BB 2/1
EAN/UPC - Product	046677478162
Order code	478164
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	929001853004
Net Weight (Piece)	0.880 kg

LED Highbay



Dimensional drawing



High Bay Mains 400W 4000K Down Light WB

Product	D	C
150HB/LED/740/ND WB DL BB 2/1	211 mm	252 mm


Photometric data



General Lighting data table and diagram.

TrueForce LED Industrial and Retail WB



TrueForce LED Industrial and Retail 150HB 740 WB



TrueForce LED Industrial and Retail 740

LED Highbay

Lifetime



LED TForce HB MV 120-100W E40 others 840 12D ND NB

LED TForce HB MV 120-100W E40 others 840 12D ND NB

