



LED Highbay

150HB/LED/750/ND WB DL BB 2/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

Product data


General Information	
Base	EX39 [Exclusionary Mogul Screw]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	50000 h
Switching Cycle	50000X
Technical Type	150-400W
Light Technical	
Color Code	750 [CCT of 5000K]
Beam Angle (Nom)	130 °
Initial lumen (Nom)	20000 lm
Luminous Flux (Rated) (Nom)	20000 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	133.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	70
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	150 W
Lamp Current (Nom)	1250 mA

Wattage Equivalent	400 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	80 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Certifications	DLC Standard
DesignLights Consortium Qualified Product List	-
Product Data	
Order product name	150HB/LED/750/ND WB DL BB 2/1
EAN/UPC - Product	046677478209
Order code	478206
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	929001853404

LED Highbay

Net Weight (Piece) 0.885 kg


Dimensional drawing




High Bay Mains 400W 5000K Down Light WB

Product	D	C
150HB/LED/750/ND WB DL BB 2/1	211 mm	252 mm


Photometric data



TrueForce LED Industrial and Retail WB



TrueForce LED Industrial and Retail 750





General Uniform Lighting Page 11

TrueForce LED Industrial and Retail 150HB 750 WB

LED Highbay

Lifetime



LED TForce HB MV 120-100W E40 others 840 12D ND NB

LED TForce HB MV 120-100W E40 others 840 12D ND NB

