



# LED PAR30 S/L

## 11.3PAR30L/PER/930/F25/DIM/120V 6/1FBT20

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	25 degree(s)
Luminous Flux	850 lm
Luminous Intensity (Nom)	4,500 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	75.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	11.3 W
Lamp Current (Nom)	120 mA


Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	185 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	11.3PAR30L/PER/930/F25/DIM/120V 6/1FBT20
Full product name	11.3PAR30L/PER/930/F25/DIM/120V 6/1FBT20

LED PAR30 S/L

Order code	535419
Material Nr. (12NC)	929001853904
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677535414



Numerator - Packs per outer box	6
EAN/UPC - Case	50046677535419

Dimensional drawing




Product	D	C
11.3PAR30L/PER/930/F25/DIM/120V 6/1FBT20	3-3/4 inch	4-5/8 inch

Photometric data



Accent Lighting Spots - 11.3PAR30L/PER/930/F25/DIM/120V 6/1FBT20

Light Distribution Diagram - 11.3PAR30L/PER/930/F25/DIM/120V 6/1FBT20




Spectral Power Distribution Colour - 11.3PAR30L/PER/930/F25/DIM/120V 6/1FBT20

LED PAR30 S/L

Lifetime



Life Expectancy Diagram - 11.3PAR30L/PER/930/F25/DIM/120V 6/1FBT20



Lumen Maintenance Diagram - 11.3PAR30L/PER/930/F25/DIM/120V 6/1FBT20

