



LED MR16

7.8MR16/PER/930/S10/Dim/EC/12V 10/1FB

Philips LED MR-16 lamps with single optic technology provide the look and color quality of traditional halogens while using a fraction of the energy. A perfect fit for spot lighting, they are compatible with most existing fixtures with MR16 GU5.3 holders and are designed as a retrofit replacement for halogen or incandescent spots.

Product data

General Information		Power Consumption	
Cap-Base	GU5.3 [GU5.3]		7.8 W
Nominal lifetime	25,000 hour(s)	Lamp Current (Nom)	880 mA
Switching Cycle	50,000	Wattage Equivalent	35 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.7
Color Code	930 [CCT of 3000K]	Voltage (Nom)	ac electronic 12 V
Beam Angle (Nom)	10 degree(s)	Temperature	
Luminous Flux	480 lm	T-Case Maximum (Nom)	221 °F
Luminous Intensity (Nom)	5,300 cd	Controls and Dimming	
Color Designation	White (WH)	Dimmable	Yes
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	61.00 lm/W	Bulb Finish	Clear
Color Consistency	<3	Bulb Material	Aluminum
Color rendering index (CRI)	95	Bulb Shape	MR16 [2inch/50mm]
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Operating and Electrical		Suitable For Accent Lighting	Yes
Line Frequency	- Hz		
Input Frequency	- Hz		

LED MR16


Energy Consumption kWh/1000 h	- kWh
-------------------------------	-------

Product Data

Order product name	7.8MR16/PER/930/S10/Dim/EC/12V 10/1FB
Full product name	7.8MR16/PER/930/S10/Dim/EC/12V 10/1FB
Order code	470146
Material Nr. (12NC)	929001872604


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677470142
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677470147

Dimensional drawing




Product	D	C
7.8MR16/PER/930/S10/Dim/EC/12V 10/1FB	2-1/16 inch	1-13/16 inch


Photometric data



Accent Lighting Spots - 7.8MR16/PER/930/S10/Dim/EC/12V 10/1FB




Spectral Power Distribution Colour - 7.8MR16/PER/930/S10/Dim/EC/12V 10/1FB




Light Distribution Diagram - 7.8MR16/PER/930/S10/Dim/EC/12V 10/1FB

LED MR16

Lifetime



Life Expectancy Diagram - 7.8MR16/PER/930/S10/Dim/EC/12V 10/1FB



Lumen Maintenance Diagram - 7.8MR16/PER/930/S10/Dim/EC/12V 10/1FB

