



# LED MR16

## 7.8MR16/PER/940/F35/Dim/EC/12V 10/1FB

Philips LED MR-16 lamps with single optic technology provide the look and color quality of traditional halogens while using a fraction of the energy. A perfect fit for spot lighting, they are compatible with most existing fixtures with MR16 GU5.3 holders and are designed as a retrofit replacement for halogen or incandescent spots.

### Product data

<b>General Information</b>			
Cap-Base	GU5.3 [GU5.3]	Power Consumption	7.8 W
Nominal lifetime	25,000 hour(s)	Lamp Current (Nom)	880 mA
Switching Cycle	50,000	Wattage Equivalent	50 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
<b>Light Technical</b>		Power Factor (Fraction)	0.7
Color Code	940 [CCT of 4000K]	Voltage (Nom)	ac electronic 12 V
Beam Angle (Nom)	35 degree(s)	<b>Temperature</b>	
Luminous Flux	540 lm	T-Case Maximum (Nom)	105 °C
Luminous Intensity (Nom)	1,450 cd	<b>Controls and Dimming</b>	
Color Designation	Cool White (CW)	Dimmable	Yes
Correlated Color Temperature (Nom)	4000 K	<b>Mechanical and Housing</b>	
Luminous Efficacy (rated) (Nom)	69.00 lm/W	Bulb Finish	Clear
Color Consistency	<3	Bulb Material	Aluminum
Color rendering index (CRI)	95	Bulb Shape	MR16 [2inch/50mm]
LLMF At End Of Nominal Lifetime (Nom)	70 %	<b>Approval and Application</b>	
<b>Operating and Electrical</b>		Suitable For Accent Lighting	Yes
Line Frequency	- Hz		
Input Frequency	- Hz		

LED MR16

Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	7.8MR16/PER/940/F35/Dim/EC/12V 10/1FB
Full product name	7.8MR16/PER/940/F35/Dim/EC/12V 10/1FB
Order code	929001873304
Material Nr. (12NC)	929001873304

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677470210
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677470215

Dimensional drawing




Product	D	C
7.8MR16/PER/940/F35/Dim/EC/12V 10/1FB	51 mm	46 mm


Photometric data



Spectral Power Distribution Colour - 7.8MR16/PER/940/F35/Dim/EC/12V 10/1FB




Accent Lighting Spots - 7.8MR16/PER/940/F35/Dim/EC/12V 10/1FB




Light Distribution Diagram - 7.8MR16/PER/940/F35/Dim/EC/12V 10/1FB

LED MR16

Lifetime



Life Expectancy Diagram - 7.8MR16/PER/940/F35/Dim/EC/12V 10/1FB



Lumen Maintenance Diagram - 7.8MR16/PER/940/F35/Dim/EC/12V 10/1FB

