

**PHILIPS**

Eco passport

## TrueForce HB 100-85W E40 840 120D GM

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in High-bay applications. The solution gives you the LED benefits of energy-efficiency and long-lifetime, plus the initial investment is low. With unique lamp design and compatibility, you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear. Multiple beam angle options and high colour-rendering index enhance the lighting distribution while creating a comfortable, safe and high-productivity environment.



Our Eco passport



### Energy

- Dimmable: No
- Energy efficiency label (EEL): A+
- Lamp Luminous Efficacy EM (Nom): 117.00 lm/W
- Power (Rated) (Nom): 85 W



### Circularity

- Nominal lifetime (nom.): 25000 h



### Packaging

- SAP Weight Paper Unit (Case): 1.159 kg
- SAP Weight Paper Unit (Piece): 0.378 kg



### Substances

- EU RoHS compliant: Yes
- RoHS mark: RoHS mark



### Weight & Materials

- Net weight (piece): 0.876 kg

Energy efficiency ranking / External awards

