



TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

TForce HB 100-85W E40 840 120D GM

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in Highbay application. The solution gives you the LED benefits of energy-efficiency and long-lifetime, plus they come for a low initial investment. With unique lamp design and compatibility, you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear. Multiple beam angle options and high colour rendering index enhance the lighting distribution while creating a comfortable, safe and high productivity environment.

Warnings and Safety

• EM version requires an EM ballast to operate. Please refer to the installation guide or consult a Philips Lighting representative.

Product data

General Information			
Cap-Base	E40 [E40]	Luminous Flux	10,000 lm
Nominal lifetime	25,000 hour(s)	Color Designation	Cool White (CW)
Switching Cycle	50,000	Correlated Color Temperature (Nom)	4000 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	117.00 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
Light Technical		Color rendering index (CRI)	80
Color Code	840 [CCT of 4000K]	LLMF At End Of Nominal Lifetime (Nom)	70 %
Beam Angle (Nom)	120 degree(s)	Operating and Electrical	
		Line Frequency	50 to 60 Hz

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Input Frequency	50 to 60 Hz
Power Consumption	85 W
Lamp Current (Nom)	715 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	110-277 V

Temperature

T-Case Maximum (Nom)	90 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	Others


Approval and Application

Energy Consumption kWh/1000 h	85 kWh
-------------------------------	--------

Product Data



Order product name	TForce HB 100-85W E40 840 120D GM
Full product name	TForce HB 100-85W E40 840 120D GM
Full product code	871869682656000
Order code	929001875708
Material Nr. (12NC)	929001875708
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696826560
Numerator - Packs per outer box	2
EAN/UPC - Case	8718696826577

Dimensional drawing



Product	D	C
TForce HB 100-85W E40 840 120D GM	190 mm	270 mm

Photometric data




General uniform lighting - TForce HB 100-85W E40 840 120D GM

Spectral Power Distribution Colour - TForce HB 100-85W E40 840 120D GM


TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Photometric data




Light Distribution Diagram - TForce HB 100-85W E40 840 120D GM

Lifetime



Lumen Maintenance Diagram - TForce HB 100-85W E40 840 120D GM



Life Expectancy Diagram - TForce HB 100-85W E40 840 120D GM

