



TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

TrueForce HB 100-85W E40 865 120D GM

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in High-bay applications. The solution gives you the LED benefits of energy-efficiency and long-lifetime, plus the initial investment is low. With unique lamp design and compatibility, you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear. Multiple beam angle options and high colour-rendering index enhance the lighting distribution while creating a comfortable, safe and high-productivity environment.

Warnings and Safety

• EM version requires an EM ballast to operate. Please refer to the installation guide or consult a Philips Lighting representative.

Product data

General Information			
Cap-Base	E40 [E40]	Luminous Flux	10,000 lm
Nominal lifetime	25,000 hour(s)	Color Designation	Cool Daylight
Switching Cycle	50,000	Correlated Color Temperature (Nom)	6500 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	117.00 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
Light Technical		Color rendering index (CRI)	80
Color Code	865 [CCT of 6500K]	LLMF At End Of Nominal Lifetime (Nom)	70 %
Beam Angle (Nom)	120 degree(s)	Operating and Electrical	
		Line Frequency	50 to 60 Hz

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Input Frequency	50 to 60 Hz
Power Consumption	85 W
Lamp Current (Nom)	715 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	110-277 V

Temperature

T-Case Maximum (Nom)	90 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	Others


Approval and Application

Energy Consumption kWh/1000 h	85 kWh
-------------------------------	--------

Product Data


Order product name	TForce HB 100-85W E40 865 120D GM
Full product name	TrueForce HB 100-85W E40 865 120D GM
Full product code	871869682660700
Order code	82660700
Material Nr. (12NC)	929001875908
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696826607
Numerator - Packs per outer box	2
EAN/UPC - Case	8718696826614

Dimensional drawing




Product	D	C
TForce HB 100-85W E40 865 120D GM	190 mm	270 mm

Photometric data




General uniform lighting - TForce HB 100-85W E40 865 120D GM



Spectral Power Distribution Colour - TForce HB 100-85W E40 865 120D GM


TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Photometric data




Light Distribution Diagram - TForce HB 100-85W E40 865 120D GM

Lifetime



Lumen Maintenance Diagram - TForce HB 100-85W E40 865 120D GM



Life Expectancy Diagram - TForce HB 100-85W E40 865 120D GM

