



TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

TrueForce HB 100-85W E40 865 120D GM

Philips TrueForce LED Industrial and Retail lamps give you a quick and easy payback solution to replace HID lamps in Highbay application. The solution gives you the LED benefits of energy-efficiency and long-lifetime, plus they come for a low initial investment. With unique lamp design and compatibility, you can directly retrofit HID lamps with TrueForce LED lamps without changing the fixtures or gear. Multiple beam angle options and high colour rendering index enhance the lighting distribution while creating a comfortable, safe and high productivity environment.

Product data

General Information		Color Designation	
Cap-Base	E40 [E40]	Color Designation	Cool Daylight
RoHS mark	RoHS mark	Correlated Color Temperature (Nom)	6500 K
Nominal Lifetime (Nom)	25000 h	Luminous Efficacy (rated) (Nom)	117.00 lm/W
Switching Cycle	50000X	Color Consistency	<6
Technical Type	85-250W	Color Rendering Index (Nom)	80
		LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical		Operating and Electrical	
Color Code	865 [CCT of 6500K]	Input Frequency	50 to 60 Hz
Beam Angle (Nom)	120 °	Power (Rated) (Nom)	85 W
Luminous Flux (Nom)	10000 lm	Lamp Current (Nom)	715 mA
Luminous Flux (Rated) (Nom)	10000 lm	Wattage Equivalent	250 W

TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Lamp Current at 220V	715 mA
Voltage (Nom)	110–277 V

Temperature

T-Case Maximum (Nom)	90 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	FR [Frosted (FR)]
-------------	--------------------

Approval and Application

Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	85 kWh


Product Data

Full product code	871869682660700
Order product name	TrueForce HB 100–85W E40 865 120D GM
EAN/UPC - Product	8718696826607
Order code	929001875908
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	2
Material Nr. (12NC)	929001875908
Net Weight (Piece)	0.876 kg

Warnings and Safety

- EM version requires an EM ballast to operate. Please refer to the installation guide or consult a Philips Lighting representative.


Dimensional drawing




High Bay 95W-10000lm 60D 6500K E40 ND

Product	D	C
TrueForce HB 100–85W E40 865 120D GM	190 mm	270 mm

Photometric data




250W E40 Others FR 120D 865 6500K



250W E40 Others FR


TrueForce LED Industrial and Retail (Highbay – HPI/SON/HPL)

Photometric data




250W E40 Others FR 120D 840 4000K

Lifetime



250W E40 Others FR



250W E40 Others FR

