



MAS LEDtube Sensor 1200mm HO 16.5W840 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescent. These T8 LED tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low energy consumption and an exceptionally long lifetime ensure this tube masters every demanding application.

Warnings and Safety

• NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.

Product data

General Information				
Cap-Base	G13 [Medium Bi-Pin Fluorescent]			
Nominal lifetime	50,000 hour(s)			
Switching Cycle	200,000			
Lighting Technology LED				
EU RoHS compliant	Yes			
Light Technical				
Color Code	840 [CCT of 4000K]			
Beam Angle (Nom)	240 degree(s)			
Luminous Flux	2,100 lm			
Color Designation	Cool White (CW)			
Correlated Color Temperature (Nom)	4000 K			
Luminous Efficacy (rated) (Nom)	127.00 lm/W			


Color Consistency	<6			
Color rendering index (CRI)	83			
LLMF At End Of Nominal Lifetime (Nom) 70 %				
Operating and Electrical				
Line Frequency	50 to 60 Hz			
Input Frequency	50 to 60 Hz			
Power Consumption	16.5 W			
Lamp Current (Max)	85 mA			
Lamp Current (Min)	65 mA			
Starting Time (Nom)	0.5 s			
Warm-up time to 60% light	0.5 s			
Power Factor (Fraction)	0.9			

Datasheet, 2023, November 24 data subject to change

Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	55 ℃
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Material	Glass
Product Length	1,200 mm
Bulb Shape	Tube, double-ended
Approval and Application	
Energy Saving Product	Yes
Approval Marks	CE marking RoHS compliance KEMA Keur
	certificate


Energy Consumption kWh/1000 h	17 kWh		
Product Data			
Order product name	MAS LEDtube Sensor 1200mm HO 16.5W840		
	Т8		
Full product name	MAS LEDtube Sensor 1200mm HO 16.5W840		
	T8		
Full product code	871869680602900		
Order code	929001878502		
Material Nr. (12NC)	929001878502		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8718696806029		
Numerator - Packs per outer box	10		
EAN/UPC - Case	8718696806036		

Dimensional drawing




Product	D1	D2	A1	A2	А3
MAS LEDtube Sensor 1200mm	25.8 mm	28 mm	1,199.4 mm	1,206.5 mm	1,213.6 mm
HO 16.5W840 T8					

Photometric data




Light Distribution Diagram - MAS LEDtube Sensor 1200mm HO 16.5W840 T8




Spectral Power Distribution Colour - MAS LEDtube Sensor 1200mm HO 16.5W840 T8


Photometric data




General uniform lighting - MAS LEDtube Sensor 1200mm HO 16.5W840 T8


Lifetime






Lumen Maintenance Diagram - MAS LEDtube Sensor 1200mm HO 16.5W840 T8








Life Expectancy Diagram - MAS LEDtube Sensor 1200mm HO 16.5W840 T8

Life Expectancy Diagram - MAS LEDtube Sensor 1200mm HO 16.5W840 T8

Lifetime



Life Expectancy Diagram - MAS LEDtube Sensor 1200mm HO 16.5W840 T8



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.