



MASTER LEDspot LV

MASTER LED 7-50W 940 MR16 24D Dim CN

Delivering intense accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot lighting. MASTER LEDspot LV is designed to replace halogen or incandescent spots. It realizes natural colors, enables cozy and comfortable ambience for residential, hospitality and emphasizes the beauty of merchandise in retail. New smaller housing provides perfect fitting with majority of luminaires in a market with a MR16 GU 5.3 holder. It not only employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V halogen electronic transformers, it also delivers high beam intensity which is equivalent to halogen MR16 spots. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers. Its high SDCM ensure stricter color consistency, that is maintained over product life. MASTER LEDspot LV delivers huge energy savings and minimizes maintenance cost without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within short period time.

Product data


General Information		Correlated Color Temperature (Nom)	4000 K
Cap-Base	GU5.3 [GU5.3]	Luminous Efficacy (rated) (Nom)	75.00 lm/W
Nominal lifetime	40,000 hour(s)	Color Consistency	<4
Switching Cycle	50,000	Color rendering index (CRI)	90
Lighting Technology	LED	LLMF At End Of Nominal Lifetime (Nom)	70 %
EU RoHS compliant	Yes	Operating and Electrical	
Light Technical		Line Frequency	- Hz
Color Code	940 [CCT of 4000K]	Input Frequency	- Hz
Beam Angle (Nom)	24 degree(s)	Power Consumption	7 W
Luminous Flux	530 lm	Lamp Current (Nom)	830 mA
Luminous Intensity (Nom)	2,700 cd	Wattage Equivalent	50 W
Color Designation	Cool White (CW)	Starting Time (Nom)	0.5 s

MASTER LEDspot LV

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes


Energy Consumption kWh/1000 h	8 kWh
Product Data	
Order product name	MASTER LED 7-50W 940 MR16 24D Dim CN
Full product name	MASTER LED 7-50W 940 MR16 24D Dim CN
Full product code	692234190545200
Order code	929001880010
Material Nr. (12NC)	929001880010
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341905452
Numerator - Packs per outer box	10
EAN/UPC - Case	6922341905469

Dimensional drawing




Product	D	C
MASTER LED 7-50W 940 MR16 24D Dim CN	50.5 mm	46.5 mm

Photometric data




Spectral Power Distribution Colour - MASTER LED 7-50W 940 MR16 24D Dim CN



Light Distribution Diagram - MASTER LED 7-50W 940 MR16 24D Dim CN

MASTER LEDspot LV


Photometric data




© 2023 Philips Lighting B.V. All rights reserved. Philips Lighting B.V. is a registered trademark of Koninklijke Philips N.V.

Accent Lighting Spots - MASTER LED 7-50W 940 MR16 24D Dim CN

Lifetime



Lumen Maintenance Diagram - MASTER LED 7-50W 940 MR16 24D Dim CN



Life Expectancy Diagram - MASTER LED 7-50W 940 MR16 24D Dim CN

