



# MASTER LEDspot LV

## MASTER LED 7-50W 927 MR16 36D Dim CN

Delivering intense accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot lighting. MASTER LEDspot LV is designed to replace halogen or incandescent spots. It realizes natural colors, enables cozy and comfortable ambience for residential, hospitality and emphasizes the beauty of merchandise in retail. New smaller housing provides perfect fitting with majority of luminaires in a market with a MR16 GU 5.3 holder. It not only employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V halogen electronic transformers, it also delivers high beam intensity which is equivalent to halogen MR16 spots. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers. Its high SDCM ensure stricter color consistency, that is maintained over product life. MASTER LEDspot LV delivers huge energy savings and minimizes maintenance cost without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within short period time.

### Product data

General Information			
Cap-Base	GU5.3 [GU5.3]	Correlated Color Temperature (Nom)	2700 K
Nominal lifetime	40,000 hour(s)	Luminous Efficacy (rated) (Nom)	71.00 lm/W
Switching Cycle	50,000	Color Consistency	<4
Lighting Technology	LED	Color rendering index (CRI)	90
EU RoHS compliant	Yes	LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical		Operating and Electrical	
Color Code	927	Line Frequency	- Hz
Beam Angle (Nom)	36 degree(s)	Input Frequency	- Hz
Luminous Flux	500 lm	Power Consumption	7 W
Luminous Intensity (Nom)	1,400 cd	Lamp Current (Nom)	830 mA
Color Designation	Warm White (WW)	Wattage Equivalent	50 W
		Starting Time (Nom)	0.5 s

# MASTER LEDspot LV


Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR16 [2inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes

Energy Consumption kWh/1000 h	8 kWh
Product Data	
Order product name	MASTER LED 7-50W 927 MR16 36D Dim CN
Full product name	MASTER LED 7-50W 927 MR16 36D Dim CN
Full product code	692234190547600
Order code	929001880110
Material Nr. (12NC)	929001880110
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341905476
Numerator - Packs per outer box	10
EAN/UPC - Case	6922341905483

## Dimensional drawing


Product	D	C
MASTER LED 7-50W 927 MR16 36D Dim CN	50.5 mm	46.5 mm

## Photometric data



Technical Parameters 14 Page Lighting LV Page 177


Accent Lighting Spots - MASTER LED 7-50W 927 MR16 36D Dim CN



Spectral Power Distribution Colour - MASTER LED 7-50W 927 MR16 36D Dim CN


# MASTER LEDspot LV

## Photometric data



Light Distribution Diagram - MASTER LED 7-50W 927 MR16 36D Dim CN

## Lifetime



Lumen Maintenance Diagram - MASTER LED 7-50W 927 MR16 36D Dim CN

Life Expectancy Diagram - MASTER LED 7-50W 927 MR16 36D Dim CN

