



# MASTER LEDspot LV

## MASTER LED 7-50W 940 MR16 36D Dim

Delivering intense accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot lighting. MASTER LEDspot LV is designed to replace halogen or incandescent spots. It realizes natural colors, enables cozy and comfortable ambience for residential, hospitality and emphasizes the beauty of merchandise in retail. New smaller housing provides perfect fitting with majority of luminaires in a market with a MR16 GU 5.3 holder. It not only employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V halogen electronic transformers, it also delivers high beam intensity which is equivalent to halogen MR16 spots. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers. Its high SDCM ensure stricter color consistency, that is maintained over product life. MASTER LEDspot LV delivers huge energy savings and minimizes maintenance cost without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within short period time.


### Product data

General Information		Correlated Color Temperature (Nom)	
Cap-Base	GU5.3 [GU5.3]		4000 K
Nominal lifetime	40,000 h	Luminous Efficacy (rated) (Nom)	75.00 lm/W
Switching Cycle	50,000	Color Consistency	<4
Lighting Technology	LED	Color rendering index (CRI)	90
EU RoHS compliant	Yes	LLMF At End Of Nominal Lifetime (Nom)	70 %
Light Technical		Operating and Electrical	
Color Code	940 [CCT of 4000K]	Line Frequency	- Hz
Beam Angle (Nom)	36 degree(s)	Input Frequency	- Hz
Luminous Flux	530 lm	Power Consumption	7 W
Luminous Intensity (Nom)	1,500 cd	Lamp Current (Nom)	830 mA
Color Designation	Cool White (CW)	Wattage Equivalent	50 W
		Starting Time (Nom)	0.5 s





# MASTER LEDspot LV

## Photometric data



Accent Lighting Spots - MASTER LED 7-50W 940 MR16 36D Dim

## Lifetime



Lumen Maintenance Diagram - MASTER LED 7-50W 940 MR16 36D Dim

Life Expectancy Diagram - MASTER LED 7-50W 940 MR16 36D Dim

