



MASTER LEDspot LV

MASTER LED 8-50W+ 830 MR16 24D Dim

Delivering intense accent beam, MASTER LEDspot LV is an ideal retrofit solution for spot lighting. MASTER LEDspot LV is designed to replace halogen or incandescent spots. It realizes natural colors, enables cozy and comfortable ambience for residential, hospitality and emphasizes the beauty of merchandise in retail. New smaller housing provides perfect fitting with majority of luminaires in a market with a MR16 GU 5.3 holder. It not only employs Philips' patented solution to guarantee the broadest possible compatibility with standard 12V halogen electronic transformers, it also delivers high beam intensity which is equivalent to halogen MR16 spots. The dimming function enables to create the desired atmosphere and it works with broad selection of dimmers. Its high SDCM ensure stricter color consistency, that is maintained over product life. MASTER LEDspot LV delivers huge energy savings and minimizes maintenance cost without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within short period time.

Product data

General Information		
Cap-Base	GU5.3 [GU5.3]	
RoHS mark	RoHS mark	
Nominal Lifetime (Nom)	40000 h	
Switching Cycle	50000X	
Technical Type	8-50W	
Light Technical		
Color Code	830 [CCT of 3000K]	
Beam Angle (Nom)	24 °	
Luminous Flux (Nom)	660 lm	
Luminous Flux (Rated) (Nom)	660 lm	
Luminous Intensity (Nom)	3250 cd	

Color Designation	White (WH)
Rated Beam Angle	24°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	82.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Power (Rated) (Nom)	8 W
Lamp Current (Nom)	960 mA

50 W

Datasheet, 2019, July 9 data subject to change


Wattage Equivalent
Starting Time (Nom)

MASTER LEDspot LV

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	12 V
Temperature	
T-Case Maximum (Nom)	100 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy Efficiency Label (EEL)	A+
Suitable For Accent Lighting	Yes


Energy Consumption kWh/1000 h	9 kWh	
Product Data		
Full product code	871869681273000	
Order product name	MASTER LED 8-50W+ 830 MR16 24D Dim	
EAN/UPC - Product	8718696812730	
Order code	929001881408	
Numerator - Quantity Per Pack	1	
Numerator - Packs per outer box	10	
Material Nr. (12NC)	929001881408	
Net Weight (Piece)	0.052 kg	


Dimensional drawing




Product	D	С
MASTER LED 8-50W+ 830 MR16 24D Dim	50.5 mm	46.5 mm

Photometric data








8-50W GU5-3 MR16


MASTER LEDspot LV


Photometric data



8-50W GU5-3 MR16 24D 827 2700K

Lifetime





7-50W GU5-3 MR16

7-50W GU5-3 MR16



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.