

**PHILIPS**

Eco passport

## 8.5MR16/LED/827/F35/DIM 12V 10/1FB MR16 LED

Philips MR16 Dimmable LED Lamps provide ambient level light to illuminate hard to maintain applications. Increased transformer compatibility allows for operation on a wider range of transformers. Available in dimmable and non-dimmable versions, these lamps are ideal for track and open recessed fixtures in retail, hospitality and residential spaces.



### Our Eco passport



#### Energy

- Intensité réglable: Yes
- Efficacité lumineuse (nominale) (nom.): 70,00 lm/W
- Power (Rated) (Nom): 8.5 W



#### Circularity

- Durée de vie (nom.): 25000 h



#### Packaging

- SAP Weight Paper Unit (Case): 0,234 kg
- SAP Weight Paper Unit (Piece): 0,008 kg



#### Substances

- EU RoHS compliant: Yes
- Marque RoHS: RoHS mark



#### Weight & Materials

- Poids net (pièce): 0,052 kg