

**PHILIPS**

Eco passport

## 5.5PL-C/LED/13V/840/IF5/P/4P 20/1 CorePro LED PL 4pin 2pin

The CorePro LED Type A - Ballast Driven (Plug and Play) InstantFit CFL-ni is a great LED solution suitable for replacing both 2-pin and 4-pin CFL fluorescent lamps, using an existing ballast. Both vertical and horizontal options are available with the horizontal version having a rotatable end cap to ensure the light is correctly aimed.



### Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



#### Energy

- Dimmable: No
- Power (Rated) (Nom): 5.5 W




#### Circularity

- Nominal Lifetime (Nom): 50000 h



#### Packaging

- SAP Weight Paper Unit (Case): 0.188 kg
- SAP Weight Paper Unit (Piece): 0.008 kg



#### Substances

- EU RoHS compliant: No



#### Weight & Materials

- Net Weight (Piece): 0.058 kg

Further reading at:  
<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2019 Signify Holding. All rights reserved.