



# BR/R LED

## 6R20/PER/850/P/E26/DIM 6/1FB

Philips Dimmable LED Reflector Lamps provide a soft, diffused level of light and smooth dimming to reduce glare. The sleek, lightweight design is ideal for downlighting.


### Product data

General Information	
Cap-Base	E26 [ Single Contact Medium Screw]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	6-45W
Light Technical	
Color Code	850 [ CCT of 5000K]
Beam Angle (Nom)	120 °
Initial lumen (Nom)	450 lm
Luminous Flux (Rated) (Nom)	450 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	75.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	6 W
Lamp Current (Nom)	53 mA
Wattage Equivalent	45 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.6 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Frosted (FR)
Product Data	
Order product name	6R20/PER/850/P/E26/DIM 6/1FB
EAN/UPC - Product	046677535247
Order code	535245
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001887804
Net Weight (Piece)	0.050 kg

# BR/R LED



## Dimensional drawing



R20 120V 6-50W 450lm 90D 5000K E26 D


Product	D	C
6R20/PER/850/P/E26/DIM 6/1FB	63 mm	94 mm

## Photometric data



45W E26 R20 FR 120D 850 5000K



45W E26 R20 FR



45W E26 R20 FR 120D 850 5000K

# BR/R LED

## Lifetime



45W E26 R20 FR

45W E26 R20 FR

