



# Classic filament LED candles and lusters

## Classic LEDCandle ND 4.3-40W E14 827 B35 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data

General Information	
Cap-Base	E14 [E14]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
Flux measurement reference	Sphere
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	109.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz

Input Frequency	50 to 60 Hz
Power Consumption	4.3 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	45 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	B35 [B 35mm]

# Classic filament LED candles and lusters

## Approval and Application


Energy Efficiency Class	F
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	387402
EyeComfort	Yes

## Product Data

Order product name	CLA LEDCandle ND 4.3-40W E14 827 B35 CL
Full product name	Classic LEDCandle ND 4.3-40W E14 827 B35 CL


Full product code	871869680853500
Order code	80853500
Material Nr. (12NC)	929001889702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696808535
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696808542

## Dimensional drawing




Product	D	C
CLA LEDCandle ND 4.3-40W E14 827 B35 CL	35 mm	97 mm

## Photometric data




Spectral Power Distribution Colour - CLA LEDCandle ND 4.3-40W E14 827 B35 CL



Light Distribution Diagram - CLA LEDCandle ND 4.3-40W E14 827 B35 CL

# Classic filament LED candles and lusters

## Photometric data




General uniform lighting - CLA LEDCandle ND 4.3-40W E14 827 B35 CL

## Lifetime



Life Expectancy Diagram - CLA LEDCandle ND 4.3-40W E14 827 B35 CL



Lumen Maintenance Diagram - CLA LEDCandle ND 4.3-40W E14 827 B35 CL

