



Classic filament LED candles and lusters



CLA LEDCandle ND 4.3-40W E14 827 B35 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information		Input Frequency	
Cap-Base	E14 [E14]	Input Frequency	50 to 60 Hz
Nominal lifetime	15,000 hour(s)	Power Consumption	4.3 W
Switching Cycle	20,000	Lamp Current (Nom)	40 mA
Lighting Technology	LED	Wattage Equivalent	40 W
Flux measurement reference	Sphere	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	45 °C
Luminous Flux	470 lm		
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	109.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	B35 [B 35mm]
Operating and Electrical			
Line Frequency	50 to 60 Hz		

Classic filament LED candles and lusters

Approval and Application


Energy Efficiency Class	F
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	387402
EyeComfort	Yes

Product Data

Order product name	CLA LEDCandle ND 4.3-40W E14 827 B35 CL
Full product name	CLA LEDCandle ND 4.3-40W E14 827 B35 CL


Full product code	871869680853500
Order code	929001889702
Material Nr. (12NC)	929001889702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696808535
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696808542

Dimensional drawing




Product	D	C
CLA LEDCandle ND 4.3-40W E14 827 B35 CL	35 mm	97 mm


Photometric data



Spectral Power Distribution Colour - CLA LEDCandle ND 4.3-40W E14 827 B35 CL





Light Distribution Diagram - CLA LEDCandle ND 4.3-40W E14 827 B35 CL



General uniform lighting - CLA LEDCandle ND 4.3-40W E14 827 B35 CL

Classic filament LED candles and lusters

Lifetime



Life Expectancy Diagram - CLA LEDCandle ND 4.3-40W E14 827 B35 CL

Lumen Maintenance Diagram - CLA LEDCandle ND 4.3-40W E14 827 B35 CL

