

**PHILIPS**

Eco passport

## 16.5PL-L/PER/22/830/IF22/P 4P 10/1 MasterClass LED PL 4pin 2pin

The MasterClass LED Type A - Ballast Driven (Plug and Play) InstantFit lamps are a great LED solution suitable for replacing both 2-pin and 4-pin CFL fluorescent lamps, using the existing ballast. Both vertical and horizontal options are available with the horizontal version having a rotatable end cap to ensure the light is correctly aimed. A wide range of color temps and lumen packages are available.



### Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.



#### Energy

- **Dimmable:** No
- **Power (Rated) (Nom):** 16.5 W



#### Circularity

- **Nominal Lifetime (Nom):** 50000 h



#### Packaging

- **SAP Weight Paper Unit (Case):** 0.410 kg
- **SAP Weight Paper Unit (Piece):** 0.015 kg



#### Substances

- **BFR policy compliant:** No
- **EU REACH restrictions compliant:** Yes
- **EU RoHS compliant:** Yes
- **EU RoHS phthalates compliant:** Yes
- **PVC policy compliant:** Yes
- **RoHS mark:** RoHS mark



#### Weight & Materials

- **Net Weight (Piece):** 0.170 kg

Further reading at:  
<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2019 Signify Holding. All rights reserved.