



CorePro LEDspot MV

Corepro LEDspot 730lm GU10 840 60D

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These GU10 LED spot lights are compatible with most existing fixtures with a GU10 LED base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance costs.

Product data


General Information			
Cap-Base	GU10 [GU10]	Input Frequency	50 to 60 Hz
Nominal lifetime	25,000 hour(s)	Power Consumption	7 W
Switching Cycle	50,000	Lamp Current (Nom)	60 mA
Lighting Technology	LED	Wattage Equivalent	100 W
EU RoHS compliant	Yes	Starting Time (Nom)	0.4 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	840 [CCT of 4000K]	T-Case Maximum (Nom)	85 °C
Beam Angle (Nom)	60 degree(s)		
Luminous Flux	730 lm	Controls and Dimming	
Luminous Intensity (Nom)	950 cd	Dimmable	No
Color Designation	Cool White (CW)		
Correlated Color Temperature (Nom)	4000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	104.00 lm/W	Bulb Shape	PAR16 [PAR 2 inch/50mm]
Color Consistency	<6		
Color rendering index (CRI)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Suitable For Accent Lighting	Yes
Luminous Flux in 90° Cone (Rated)	730 lm	Energy Consumption kWh/1000 h	7 kWh
Operating and Electrical			
Line Frequency	50 to 60 Hz		

CorePro LEDspot MV

Product Data	
Order product name	Corepro LEDspot 730lm GU10 840 60D
Full product name	Corepro LEDspot 730lm GU10 840 60D
Full product code	871869681335500
Order code	929001895202
Material Nr. (12NC)	929001895202


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696813355
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696813362

Dimensional drawing




Product	D	C
Corepro LEDspot 730lm GU10 840 60D	50 mm	54 mm


Photometric data



Light Distribution Diagram - Corepro LEDspot 730lm GU10 840 60D



Spectral Power Distribution Colour - Corepro LEDspot 730lm GU10 840 60D




Accent Lighting - Spots

Accent Lighting Spots - Corepro LEDspot 730lm GU10 840 60D

CorePro LEDspot MV

Lifetime



Life Expectancy Diagram - Corepro LEDspot 730lm GU10 840 60D

Lumen Maintenance Diagram - Corepro LEDspot 730lm GU10 840 60D

