



Classic filament LEDbulbs

CLA LEDBulb D 5.5-40W ST64 E27 827 CL

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information			
Cap-Base	E27 [E27]	Power Consumption	5.5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	38 mA
Switching Cycle	20,000	Wattage Equivalent	40 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	40 °C
Luminous Flux	470 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Yes
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	85.00 lm/W	Bulb Finish	Clear
Color Consistency	<6	Bulb Shape	ST64
Color rendering index (CRI)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Consumption kWh/1000 h	6 kWh
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

EyeComfort	Yes
Product Data	
Order product name	CLA LEDBulb D 5.5-40W ST64 E27 827 CL
Full product name	CLA LEDBulb D 5.5-40W ST64 E27 827 CL
Full product code	871869681425300
Order code	929001895402


Material Nr. (12NC)	929001895402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696814253
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696814260

Dimensional drawing




Product	D	C
CLA LEDBulb D 5.5-40W ST64 E27 827 CL	64 mm	140 mm


Photometric data



Light Distribution Diagram - CLA LEDBulb D 5.5-40W ST64 E27 827 CL




Spectral Power Distribution Colour - CLA LEDBulb D 5.5-40W ST64 E27 827 CL




General uniform lighting - CLA LEDBulb D 5.5-40W ST64 E27 827 CL

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - CLA LEDBulb D 5.5-40W ST64 E27 827 CL



Lumen Maintenance Diagram - CLA LEDBulb D 5.5-40W ST64 E27 827 CL

