



# Classic LEDspotMV

LEDClassic 35W GU10 2700K 127V 36D D


## Dados do produto

General Information	
Cap-Base	GU10 [ GU10]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	4.5-35W
Light Technical	
Color Code	827 [ TCC de 2700K]
Beam Angle (Nom)	36 °
Luminous Flux (Nom)	350 lm
Luminous Flux (Rated) (Nom)	350 lm
Luminous Intensity (Nom)	600 cd
Color Designation	Branco quente (WW)
Rated Beam Angle	36 °
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	77.00 lm/W
Color Consistency	<6
Índice de restituição cromática (Nom.)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50-60 Hz
Power (Rated) (Nom)	4.5 W
Lamp Current (Nom)	45 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s

Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	127 V
Temperature	
T-máxima na caixa (Nom)	85 °C
Controls and Dimming	
Dimmable	Sim
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Efficiency Label (EEL)	A+
Product Data	
Full product code	871869682036000
Order product name	LEDClassic 35W GU10 2700K 127V 36D D
EAN/UPC - Product	8718696820360
Order code	929001911711
Local Code	929001911711
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001911711
Net Weight (Piece)	0.040 kg

# Classic LEDspotMV


## Desenho dimensional




GU10 127V 5.2-35W 350lm 36D 2700K D

Product	D	C
LEDClassic 35W GU10 2700K 127V 36D D	50.5 mm	54.5 mm


## Dados fotométricos



LEDspot Classic 35W GU10 PAR16 827 127V 36D DIM





LEDspot Classic 35W GU10 PAR16 827 127V 36D DIM



LEDspot Classic 35W GU10 PAR16 827 127V 36D DIM

# Classic LEDspotMV

## Vida útil



LEDspot Classic 50W GU10 PAR16 827 36D ND

LEDspot Classic 50W GU10 PAR16 827 36D ND

