



Classic LEDspotMV

LEDClassic 50W GU10 827 100-240V 36D ND


Dados do produto

General Information	
Cap-Base	GU10 [GU10]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	6-50W
Light Technical	
Color Code	827 [TCC de 2700K]
Beam Angle (Nom)	36 °
Luminous Flux (Nom)	525 lm
Luminous Flux (Rated) (Nom)	525 lm
Luminous Intensity (Nom)	800 cd
Color Designation	Branco quente (WW)
Rated Beam Angle	36 °
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	87.00 lm/W
Color Consistency	<6
Índice de restituição cromática (Nom.)	80
Llmf At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50-60 Hz
Power (Rated) (Nom)	6 W
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7

	50 mA
	37 mA
Voltage (Nom)	127-220 V
Temperature	
T-máxima na caixa (Nom)	75 °C
Controls and Dimming	
Dimmable	Não
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Efficiency Label (EEL)	A+
Product Data	
Full product code	871869682030800
Order product name	LEDClassic 50W GU10 827 100-240V 36D ND
EAN/UPC - Product	8718696820308
Order code	929001911911
Local Code	929001911911
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001911911
Net Weight (Piece)	0.040 kg

Classic LEDspotMV


Desenho dimensional




GU10 5.6-50W 525lm 36D 2700K ND

Product	D	C
LEDClassic 50W GU10 827 100-240V 36D ND	50.5 mm	54.5 mm


Dados fotométricos



LEDspot Classic 50W GU10 PAR16 827 36D ND





LEDspot Classic 50W GU10 PAR16 827 36D ND



Classic LEDspotMV

Vida útil



LEDspot Classic 50W GU10 PAR16 827 36D ND

LEDspot Classic 50W GU10 PAR16 827 36D ND

