



# TrueForce High Lumen PAR

## 36PAR38/PER/830/S15/ND/120V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

### Product data


General Information			
Cap-Base	E26 [Single Contact Medium Screw]	Power Consumption	36 W
Nominal lifetime	25,000 hour(s)	Lamp Current (Nom)	330 mA
Switching Cycle	50,000	Wattage Equivalent	250 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.95
Color Code	830 [CCT of 3000K]	Voltage (Nom)	120 V
Beam Angle (Nom)	15 degree(s)	Temperature	
Luminous Flux	3,800 lm	T-Case Maximum (Nom)	90 °C
Luminous Intensity (Nom)	31,000 cd	Controls and Dimming	
Color Designation	White (WH)	Dimmable	No
Correlated Color Temperature (Nom)	3000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	105.00 lm/W	Bulb Finish	Clear
Color Consistency	<4	Bulb Material	Aluminum
Color rendering index (CRI)	80	Bulb Shape	PAR38 [PAR 4.75 inch/121mm]
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Operating and Electrical		Suitable For Accent Lighting	Yes
Line Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	- kWh
Input Frequency	50 to 60 Hz		

TrueForce High Lumen PAR

Energy Certifications	Energy Star
Product Data	
Order product name	36PAR38/PER/830/S15/ND/120V 6/1FB
Full product name	36PAR38/PER/830/S15/ND/120V 6/1FB
Order code	534586
Material Nr. (12NC)	929001916604


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677534585
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677534580

Dimensional drawing




Product	D	C
36PAR38/PER/830/S15/ND/120V 6/1FB	123 mm	133 mm


Photometric data



Spectral Power Distribution Colour - 36PAR38/PER/830/S15/ND/120V 6/1FB




Light Distribution Diagram - 36PAR38/PER/830/S15/ND/120V 6/1FB




Accent Lighting Spots - 36PAR38/PER/830/S15/ND/120V 6/1FB

TrueForce High Lumen PAR

Lifetime



Life Expectancy Diagram - 36PAR38/PER/830/S15/ND/120V 6/1FB



Lumen Maintenance Diagram - 36PAR38/PER/830/S15/ND/120V 6/1FB

