



# TrueForce High Lumen PAR

## 33PAR38/PER/830/F25/DIM/120V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.


### Product data

General Information		Power (Rated) (Nom)	
Cap-Base	E26 [ Single Contact Medium Screw]		33 W
Nominal Lifetime (Nom)	25000 h	Lamp Current (Nom)	300 mA
Switching Cycle	50000X	Starting Time (Nom)	0.5 s
Technical Type	33-250W	Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.95
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	830 [ CCT of 3000K]	T-Case Maximum (Nom)	90 °C
Beam Angle (Nom)	25 °		
Luminous Flux (Nom)	3000 lm	Controls and Dimming	
Luminous Flux (Rated) (Nom)	3000 lm	Dimmable	Yes
Luminous Intensity (Nom)	10000 cd	Approval and Application	
Color Designation	White (WH)	Suitable For Accent Lighting	Yes
Rated Beam Angle	25 °	Product Data	
Correlated Color Temperature (Nom)	3000 K	Order product name	33PAR38/PER/830/F25/DIM/120V 6/1FB
Luminous Efficacy (rated) (Nom)	90.00 lm/W	EAN/UPC - Product	046677534615
Color Consistency	<4	Order code	534610
Color Rendering Index (Nom)	80	Numerator - Quantity Per Pack	1
LLMF At End Of Nominal Lifetime (Nom)	70 %	Numerator - Packs per outer box	6
Operating and Electrical			
Input Frequency	50 to 60 Hz		

# TrueForce High Lumen PAR

Material Nr. (12NC)	929001916904
Net Weight (Piece)	0.425 kg


## Dimensional drawing



PAR38 120V 32-W 2800lm 25D 3000K E26 D


Product	D	C
33PAR38/PER/830/F25/DIM/120V 6/1FB	123 mm	133 mm

## Photometric data




Product Information v1 Page Lighting v1 Page 11

LEDSpot 33W E26 PAR38 F25





LEDSpot 33W E26 PAR38 F25



LEDSpot 33W E26 PAR38

# TrueForce High Lumen PAR

## Lifetime



LEDSpot 33W E26 PAR38

LEDSpot 33W E26 PAR38

