



# TrueForce High Lumen PAR

## 25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

### Product data

General Information	
Cap-Base	E26 [ Single Contact Medium Screw]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	25.5-75W

Light Technical	
Color Code	830 [ CCT of 3000K]
Beam Angle (Nom)	15 °
Luminous Flux (Nom)	2500 lm
Luminous Flux (Rated) (Nom)	2500 lm
Luminous Intensity (Nom)	16000 cd
Color Designation	White (WH)
Rated Beam Angle	15 °
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	98.00 lm/W
Color Consistency	<4
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz

Power (Rated) (Nom)	25.5 W
Lamp Current (Max)	230 mA
Lamp Current (Min)	115 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.8
Voltage (Nom)	120-277 V

Temperature	
T-Case Maximum (Nom)	95 °C

Controls and Dimming	
Dimmable	No

Approval and Application	
Suitable For Accent Lighting	Yes


Product Data	
Order product name	25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB
EAN/UPC - Product	046677534646
Order code	534644

# TrueForce High Lumen PAR

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001917004

Net Weight (Piece)	0.290 kg
--------------------	----------



## Dimensional drawing



PAR30L 27.5-W 2300lm 15D 3000K E26 ND


Product	D	C
25.5PAR30L/PER/830/S15/ND/120-277V 6/1FB	96 mm	119 mm

## Photometric data



LEDspot PAR30 1FB



LEDspot 25,5 PAR30L 830 S15



LEDspot 25,5 PAR30L 830 S15

# TrueForce High Lumen PAR

## Lifetime



LEDspot PAR30 1FB

LEDspot PAR30 1FB

