



# TrueForce High Lumen PAR

## 33PAR38/PER/830/S15/DIM/120V B 6/1FB

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

### Product data

General Information		Power Consumption	
Cap-Base	E26 [Single Contact Medium Screw]	Power Consumption	33 W
Nominal lifetime	25,000 hour(s)	Lamp Current (Nom)	300 mA
Switching Cycle	50,000	Wattage Equivalent	250 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.95
		Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	Ambient temperature range	-20 to +45 °C
Beam Angle (Nom)	15 degree(s)	T-Case Maximum (Nom)	90 °C
Luminous Flux	3,000 lm		
Luminous Intensity (Nom)	33,000 cd	Controls and Dimming	
Color Designation	White (WH)	Dimmable	Only with specific dimmers
Correlated Color Temperature (Nom)	3000 K		
Luminous Efficacy (rated) (Nom)	90 lm/W	Mechanical and Housing	
Color Consistency	<4	Bulb Finish	Clear
Color rendering index (CRI)	80	Bulb Material	Metal
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	PAR38
		UL Wet/ damp/ dry location	Damp location
Operating and Electrical			
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

# TrueForce High Lumen PAR

## Approval and Application

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Energy Certifications	Energy Star
T20 compliant	N/A

## Application Conditions


can it be used in closed luminaires	No
-------------------------------------	----

## Product Data

Order product name	33PAR38/PER/830/S15/DIM/120V B 6/1FB
--------------------	--------------------------------------



Full product name	33PAR38/PER/830/S15/DIM/120V B 6/1FB
Order code	929001919604
Material Nr. (12NC)	929001919604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677534622
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677534627

## Dimensional drawing



Product	D	C
33PAR38/PER/830/S15/DIM/120V B 6/1FB	123 mm	133 mm

## Photometric data




Light Distribution Diagram - 33PAR38/PER/830/S15/DIM/120V B 6/1FB

Spectral Power Distribution Colour - 33PAR38/PER/830/S15/DIM/120V B 6/1FB


# TrueForce High Lumen PAR

## Photometric data




Accent Lighting Spots - 33PAR38/PER/830/S15/DIM/120V B 6/1FB

## Lifetime



Life Expectancy Diagram - 33PAR38/PER/830/S15/DIM/120V B 6/1FB



Lumen Maintenance Diagram - 33PAR38/PER/830/S15/DIM/120V B 6/1FB

