PHILIPS Lighting

CorePro LED PLL



CorePro LED PLL HF 24W 840 4P 2G11

Philips CorePro LED PLL is the ideal uplamping solution for downlights & luminaires in a wide range of general lighting applications. It integrates a LED light source into a traditional fluorescent form factor to offer superb energy savings over a lifetime that's twice as long as fluorescent alternatives.

Product data

General Information					
Cap-Base	2G11				
Nominal lifetime	30,000 hour(s)				
Switching Cycle	50,000				
Lighting Technology	LED				
Flux measurement reference	Sphere				
CE mark	Yes				
EU RoHS compliant	Yes				
Light Technical					
Color Code	840 [CCT of 4000K]				
Beam Angle (Nom)	160 degree(s)				
Luminous Flux	3,400 lm				
Color Designation	Cool White (CW)				
Correlated Color Temperature (Nom)	4000 K				
Luminous Efficacy (rated) (Nom)	141.00 lm/W				
Color Consistency	<6				
Color rendering index (CRI)	83				
LLMF At End Of Nominal Lifetime (Nom)	70 %				
Photobiological safety according to EN 62471	RGO				
Operating and Electrical					

20000-70000 Hz

Input Frequency 20000-70000 Hz **Power Consumption** 24 W 600 mA Lamp Current (Max) Lamp Current (Min) 400 mA Starting Time (Nom) 0.5 s Warm-up time to 60% light 0.5 s Power Factor (Fraction) 0.9 53-77 V Voltage (Nom) LED alternative to fluorescent lamp power 55 W Inrush current at mains _ Max. lamp no. on MCB B type 10A - Mains _ Max. lamp no. on MCB B type 10A - EM ballast without Comp. Cap. Max. lamp no. on MCB B type 10A - EM ballast _ with Comp. Cap. Max. lamp no. on MCB B type 16A - Mains Max. lamp no. on MCB B type 16A - EM ballast without Comp. Cap. Max. lamp no. on MCB B type 16A - EM ballast _ with Comp. Cap. Ballast Compatibility HF


Line Frequency

CorePro LED PLL

Temperature	
Ambient temperature range	-20 ℃ to 45 ℃
T-Case Maximum (Nom)	70 ℃
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	540 mm
Bulb Shape	PL-L
Approval and Application	
Energy Efficiency Class	E
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance
	KEMA Keur certificate
Energy Consumption kWh/1000 h	24 kWh


EPREL Registration Number	387356
Product Data	
Order product name	CorePro LED PLL HF 24W 840 4P
	2G11
Full product name	CorePro LED PLL HF 24W 840 4P
	2G11
Full product code	871869682841000
Order code	929001920502
Material Nr. (12NC)	929001920502
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696828410
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696828427

Dimensional drawing




Product	D	D1	A1	A2	A3
CorePro LED PLL HF 24W 840 4P 2G11	37.6 mm	17 mm	453 mm	528.5 mm	535.1 mm

Photometric data




Light Distribution Diagram - CorePro LED PLL HF 24W 840 4P 2G11



General uniform lighting - CorePro LED PLL HF 24W 840 4P 2G11


CorePro LED PLL

Photometric data





Spectral Power Distribution Colour - CorePro LED PLL HF 24W 840 4P 2G11


Lifetime



















CorePro LED PLL

Lifetime



Lumen Maintenance Diagram - CorePro LED PLL HF 24W 840 4P 2G11



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, March 15 - data subject to change