



MASTER LEDtube EM/ Mains T8



MAS LEDtube 1500mm HO 18.2W 865 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescent. These T8 LED tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low energy consumption and an exceptionally long lifetime ensure this tube masters every demanding application.

Warnings and Safety

- NOTE: The overall energy efficiency and light distribution of any installation that uses these lamps will be determined by the design of the installation.

Product data

General Information		Correlated Color Temperature (Nom)		6500 K
Cap-Base	G13 ROT	Luminous Efficacy (rated) (Nom)		170 lm/W
Nominal lifetime	75,000 hour(s)	Color Consistency		<6
Switching Cycle	200,000	Color rendering index (CRI)		80
Lighting Technology	LED	LLMF At End Of Nominal Lifetime (Nom)		70 %
Flux measurement reference	Sphere	Flickering value (PstLM) - Flickering value as per EN 61000-3-3		0.5
CE mark	Yes	Stroboscopic effect visibility measure (SVM)		0.2
EU RoHS compliant	Yes	Photobiological safety according to EN 62471		RGO
Light Technical		Operating and Electrical		
Color Code	865 [CCT of 6500K]	Line Frequency		50 to 60 Hz
Beam Angle (Nom)	160 degree(s)	Input Frequency		50 to 60 Hz
Luminous Flux	3,100 lm	Power Consumption		18.2 W
Color Designation	Cool Daylight			

MASTER LEDtube EM/Mains T8

Lamp Current (Max)	93 mA
Lamp Current (Min)	77 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	58 W
Inrush current at mains	8.4
Max. lamp no. on MCB B type 10A - Mains	80
Max. lamp no. on MCB B type 10A – EM ballast without Comp. Cap.	80
Max. lamp no. on MCB B type 10A – EM ballast with Comp. Cap.	10
Max. lamp no. on MCB B type 16A - Mains	130
Max. lamp no. on MCB B type 16A – EM ballast without Comp. Cap.	135
Max. lamp no. on MCB B type 16A – EM ballast with Comp. Cap.	16
Ballast Compatibility	EM/Mains

Temperature

Ambient temperature range	-20 °C to 45 °C
T-Case Maximum (Nom)	55 °C

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
-------------	---------

Bulb Material	Plastic
Product Length	1,500 mm
Bulb Shape	T8


Approval and Application

Energy Efficiency Class	C
Energy Saving Product	Yes
Approval Marks	RoHS compliance TUV CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	19 kWh
EPREL Registration Number	1206971

Product Data

Order product name	MAS LEDtube 1500mm HO 18.2W 865 T8
Full product name	MAS LEDtube 1500mm HO 18.2W 865 T8
Full product code	871869959245500
Order code	929001923102
Material Nr. (12NC)	929001923102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699592455
Numerator - Packs per outer box	10
EAN/UPC - Case	8718699592462



Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 1500mm HO 18.2W 865 T8	25.8 mm	28 mm	1,498.8 mm	1,505.9 mm	1,513 mm


MASTER LEDtube EM/Mains T8

Photometric data




Spectral Power Distribution Colour - MAS LEDtube 1500mm HO 18.2W 865 T8

General uniform lighting - MAS LEDtube 1500mm HO 18.2W 865 T8




Light Distribution Diagram - MAS LEDtube 1500mm HO 18.2W 865 T8

Lifetime





Lumen Maintenance Diagram - MAS LEDtube 1500mm HO 18.2W 865 T8



Life Expectancy Diagram - MAS LEDtube 1500mm HO 18.2W 865 T8


MASTER LEDtube EM/Mains T8

Lifetime



Lumen Maintenance Diagram - MAS LEDtube 1500mm HO 18.2W 865 T8

Life Expectancy Diagram - MAS LEDtube 1500mm HO 18.2W 865 T8



Life Expectancy Diagram - MAS LEDtube 1500mm HO 18.2W 865 T8

